



# **SAFETY MASK**

## **CATALOGUE**

## Freaquer Facemask

Freaquer Corporation designs and manufactures a wide range of protective Facemasks for the laboratory, cleanroom and light industrial markets. With a variety of protective products and configurations, we have just the right one for your specific environment and/or application.

Many of our Facemasks incorporate Freaquer patented and integrated Magic Arch<sup>®</sup> and PFL<sup>®</sup> (Positive Facial Lock) feature that enhance user comfort and product performance.

## FQ<sup>®</sup> Masks

### Breathe Easier and Safer

**Features & Benefits:** The innovative and patented Positive Facial Lock<sup>®</sup> (FQ<sup>®</sup>) feature utilizes our exclusive Twist-Seal<sup>®</sup> technology that allows the user to create a custom fit each and everytime. This unique feature significantly reduces the possibility of the user inhaling airborne contaminants and creates a positive seal to a variety of facial sizes and features. Additionally, the integrated Magic Arch<sup>®</sup> prevents the mask from coming in contact with the user's nose and mouth thereby making it easier to breathe while enhancing filtration efficiency. The hypoallergenic materials used in the PFL masks create a durable exterior and a soft, comfortable interior.

Table 1 - Medical Facemask Material Requirements by Performance Class Per ASTM F2100	
Characteristic	
Bacterial Filtration Efficiency, %	≥ 95
Differential Pressure, mm H <sub>2</sub> O/cm <sup>2</sup>	<4.0
Sub-micron Particulate Filtration Efficiency at 0.1 micron, %	Not Required
Resistance to Penetration by synthetic blood, minimum pressure in mm Hg for pass result	80
Flame spread	Class 1
Helmke Drum	Category 2



608 PD

### FQ<sup>®</sup> Headband Masks

608 Blue  
608 BS Blue Stripe  
608 PD Purple Designer

300/case (6 boxes of 50)

9608 White

Cleanroom Packaging  
300/case (6 bags of 50)



615 BS

### FQ<sup>®</sup> Ear Loop Masks

615 Blue  
615 BS Blue Stripe  
615 PD Purple Designer  
615 PK Pink Stripe

300/case (6 boxes of 50)



108


### FQ<sup>®</sup> Headband Masks No Magic Arch<sup>®</sup>

108 Blue

300/case (6 boxes of 50)

9908 Blue

Cleanroom Packaging  
300/case (6 bags of 50)



115

### FQ<sup>®</sup> Ear Loop Masks No Magic Arch<sup>®</sup>

115 Blue

300/case (6 boxes of 50)

## FQ<sup>®</sup> Laser Masks

### FQ<sup>®</sup> Technology and Laser Plume Protection

**Features & Benefits:** The FQ<sup>®</sup> Laser mask effectively filters plumes during laser surgery. The mask utilizes Positive Facial Lock<sup>®</sup> technology with an integrated Twist-Seal<sup>®</sup> chinpiece in the facemask to give everyone in the operating room a custom fit each time. The FQ<sup>®</sup> design helps eliminate the potential of inhaling airborne contaminants while maintaining a comfortable

seal to the user's face. The patented and integrated Magic Arch<sup>®</sup> technology prevents the mask from coming in contact with the user's nose and mouth thereby making it easier to breathe while enhancing filtration efficiency. These durable masks are made of hypoallergenic materials and have a smooth, soft interior for ultimate comfort.



638

#### FQ<sup>®</sup> Laser Masks

638 Gray Stripe,  
Single Headband

210/case (6 boxes of 35)

Table 1 - Medical Facemask Material Requirements by Performance Class Per ASTM F2100	
Characteristic	
Bacterial Filtration Efficiency, %	≥ 98
Differential Pressure, mm H <sub>2</sub> O/cm <sup>2</sup>	<5.0
Sub-micron Particulate Filtration Efficiency at 0.1 micron, %	≥ 98
Resistance to Penetration by synthetic blood, minimum pressure in mm Hg for pass result	120
Flame spread	Class 1
Helmke Drum	Category 2

## FQ<sup>®</sup> N-95 Particulate Respirator

### NIOSH Approved Respirator

**Features & Benefits:** The Positive Facial Lock<sup>®</sup> (FQ<sup>®</sup>) N-95 Particulate Respirator meets the World Health Organization (WHO) and the Centers for Disease Control (CDC) recommended protection levels (where applicable) for many airborne contaminants. NIOSH Certified, our N-95 delivers the appropriate amount of filtration efficiency and when combined with a trio of patented and unique design features,

also delivers the user a comfortable, custom fitting facemask. The integrated Magic Arch<sup>®</sup> technology creates a breathing chamber within the facemask by holding it away from the user's nose and mouth. Our PFL technology, incorporating an integrated Twist Seal<sup>®</sup> chinpiece, helps the wearer create a perfect fit every time.



695

#### FQ<sup>®</sup> N95 Particulate Respirator

695 Teal Stripe

210/case (6 boxes of 35)

Table 1 - Medical Facemask Material Requirements by Performance Class Per ASTM F2100	
Characteristic	
Bacterial Filtration Efficiency, %	≥ 95
Differential Pressure, mm H <sub>2</sub> O/cm <sup>2</sup>	<4.0
Sub-micron Particulate Filtration Efficiency at 0.1 micron, %	Not Required
Resistance to Penetration by synthetic blood, minimum pressure in mm Hg for pass result	80
Flame spread	Class 1
Helmke Drum	Category 2

## CoolOne™ Facemasks

### Cool Design, Very Cool Comfort

**Features & Benefits:** Thanks to the patented Magic Arch® support, CoolOne facemasks give users cooler, more comfortable performance than other designs currently on the market. The integrated Magic Arch® support strip holds the mask away from the nose and mouth to create a larger breathing chamber to enhance user comfort. Choose from tie strings, ear loops or ear loops with an anti-fog application - for use in high humidity environments or with protective eyewear.



BL 6055

### CoolOne™ Ear Loop Masks

BL 6055 Blue  
GR 6055 Green  
PK 6055 Pink  
YL 6055 Yellow

500/case (10 boxes of 50)

### CoolOne™ Anti-fog Ear Loop Masks

BL 6155 Blue

500/case (10 boxes of 50)



BL 6001

### CoolOne™ Tie Mask

BL 6001 Blue

300/case (6 boxes of 50)

BL 6001 CC

Cleanroom Packaging  
300/case (6 bags of 50)

**Table 1 - Medical Facemask Material Requirements by Performance Class Per ASTM F2100**

Characteristic	
Bacterial Filtration Efficiency, %	≥ 95
Differential Pressure, mm H <sub>2</sub> O/cm <sup>2</sup>	<4.0
Sub-micron Particulate Filtration Efficiency at 0.1 micron, %	Not Required
Resistance to Penetration by synthetic blood, minimum pressure in mm Hg for pass result	80
Flame spread	Class 1
Helmke Drum	Category 1

## CoolOne™ Facemasks

### For Sensitive Skin

**Features & Benefits:** If you have skin sensitivity, choose the CoolOne Sensitive Skin facemask. These facemasks are hypoallergenic and free of pigments and dyes. The patented Magic Arch® support strip holds the mask away from the nose and mouth to create a larger breathing chamber to enhance user comfort. For a secure and comfortable fit, soft knit ear loops are available along with an anti-fog version for use in high humidity environments or with protective eyewear.



WH 6155

### CoolOne™ Sensitive Skin Ear Loop Mask

WH 1155 White

500/case (10 boxes of 50)

### CoolOne™ Sensitive Skin Anti-Fog Ear Loop Mask

WH 6155 White

500/case (10 boxes of 50)

**Table 1 - Medical Facemask Material Requirements by Performance Class Per ASTM F2100**

Characteristic	
Bacterial Filtration Efficiency, %	≥ 95
Differential Pressure, mm H <sub>2</sub> O/cm <sup>2</sup>	<4.0
Sub-micron Particulate Filtration Efficiency at 0.1 micron, %	Not Required
Resistance to Penetration by synthetic blood, minimum pressure in mm Hg for pass result	80
Flame spread	Class 1
Helmke Drum	Category 1

## ShieldMate® Facemask w/Eye Shield

### Dual Protective Performance

**Features & Benefits:** Get both eye and face splash protection along with particulate filtration efficiency in this truly unique design. The ShieldMate®, a combination facemask and eye shield, features a low glare, anti-fog coated, optically clear shield that is ultrasonically welded to the facemask. Additionally, an anti-fog foam strip on the top of the facemask significantly reduces the potential for eyewearfogging. The patented Magic

Arch® support strip holds the mask away from the nose and mouth creating a larger breathing chamber to enhance user comfort. This results in a cooler, more comfortable performance for the wearer. Comfortable tie strings and a full-length aluminum nose-piece properly secure the ShieldMate facemask to the user.



BL 8101S

### ShieldMate® Mask w/Eye Shield

BL 8101S Blue

100/case (4 boxes of 25)

**Table 1 - Medical Facemask Material Requirements by Performance Class Per ASTM F2100**

Characteristic	
Bacterial Filtration Efficiency, %	≥ 95
Differential Pressure, mm H <sub>2</sub> O/cm <sup>2</sup>	<4.0
Sub-micron Particulate Filtration Efficiency at 0.1 micron, %	Not Required
Resistance to Penetration by synthetic blood, minimum pressure in mm Hg for pass result	80
Flame spread	Class 1
Helmke Drum	Category 2

## Combo® Facemask w/Shield

### Optically Clear, Removable Shield

**Features & Benefits:** The Combo® facemask and face shield is hypoallergenic with an optically clear shield. The face shield is attached to the mask with snaps so that it can be easily removed where applicable. The faceshield is 7 millimeters thick with an anti-fog coating, low glare and is distortion free.



5194-E

### ShieldMate® Mask w/Shield

5194-E Blue

100/case (4 boxes of 25)

**Table 1 - Medical Facemask Material Requirements by Performance Class Per ASTM F2100**

Characteristic	
Bacterial Filtration Efficiency, %	≥ 98
Differential Pressure, mm H <sub>2</sub> O/cm <sup>2</sup>	<5.0
Sub-micron Particulate Filtration Efficiency at 0.1 micron, %	≥ 98
Resistance to Penetration by synthetic blood, minimum pressure in mm Hg for pass result	160
Flame spread	Class 1
Helmke Drum	Category 1

## Freaquer Air® Facemasks

### Particle Filtration to 0.1 Micron

**Features & Benefits:** The high value FreaquerAir® facemasks are clean, comfortable and provide outstanding particle filtration down to 0.1 micron. The full-length aluminum nosepiece helps provide a perfect fit every time. The sonic welded design ensures maximum protection for the user. The FreaquerAir® is available with either ear loops or tie strings.



YL 5005

### FreaquerAir® Ear Loop Masks

BL 5005      Blue  
 GR 5005      Green  
 PK 5005      Pink  
 YL 5005      Yellow

500/case (10 boxes of 50)



BL 5100

### FreaquerAir® Tie Mask

BL 5100      Blue

300/case (6 boxes of 50)

Table 1 - Medical Facemask Material Requirements by Performance Class Per ASTM F2100	
Characteristic	
Bacterial Filtration Efficiency, %	≥ 98
Differential Pressure, mm H <sub>2</sub> O/cm <sup>2</sup>	<5.0
Sub-micron Particulate Filtration Efficiency at 0.1 micron, %	≥ 98
Resistance to Penetration by synthetic blood, minimum pressure in mm Hg for pass result	160
Flame spread	Class 1
Helmke Drum - Ear Loops	Category 1
Helmke Drum - Ties	Category 2

## Microbreathe™ Facemask

### Designed for Cleanroom Use

**Features & Benefits:** The interior of this 3-ply facemask is made of a soft, lightweight thermal bond material that provides the user with a comfortable fit. The hypoallergenic design provides high filtration efficiency while remaining a very breathable facemask. The facemask uses soft, non-latex elastic ear loops that are ultrasonically welded on the sides.



9010

### Microbreathe™ Ear Loop Mask

9010      White

Cleanroom Packaging  
 500/case (10 bags of 50)

Table 1 - Medical Facemask Material Requirements by Performance Class Per ASTM F2100	
Characteristic	
Bacterial Filtration Efficiency, %	≥ 98
Differential Pressure, mm H <sub>2</sub> O/cm <sup>2</sup>	<5.0
Sub-micron Particulate Filtration Efficiency at 0.1 micron, %	≥ 98
Resistance to Penetration by synthetic blood, minimum pressure in mm Hg for pass result	120
Flame spread	Class 1
Helmke Drum	Category 1

## FreaquerGuard® Facemask

### Suitable for Use in Controlled Environments

**Features & Benefits:** For superior comfort and protection, the hypoallergenic FreaquerGuard facemask exhibits an excellent water vapor transmission rate and particle filtration down to 0.1 micron. This 3-ply facemask has soft, latex-free, non-irritating knit ear loops that are ultrasonically welded to the mask.



9050

### FreaquerGuard® Ear Loop Mask

9050 Blue

Cleanroom Packaging  
500/case (10 bags of 50)

Table 1 - Medical Facemask Material Requirements by Performance Class Per ASTM F2100	
Characteristic	
Bacterial Filtration Efficiency, %	≥ 98
Differential Pressure, mm H <sub>2</sub> O/cm <sup>2</sup>	<5.0
Sub-micron Particulate Filtration Efficiency at 0.1 micron, %	≥ 98
Resistance to Penetration by synthetic blood, minimum pressure in mm Hg for pass result	160
Flame spread	Class 1
Helmke Drum	Category 1

## MVT Facemasks

### Highly Breathable

**Features & Benefits:** This hypoallergenic MVT highly breathable facemask is comfortable to wear while providing limited filtration efficiency. The soft inner facing provides for all-day comfort and the ultrasonic weld design yields a complete facial seal every time. Available with comfortable, soft, latex-free knit ear loops or polyethylene tie strings.



9040

### MVT Ear Loop Mask

9040 White

Cleanroom Packaging  
500/case (10 bags of 50)



9240

### MVT Tie Mask

9240 White

Cleanroom Packaging  
500/case (10 bags of 50)

Performance	Test Performed	Result (Average)
	Differential Pressure per MIL-M36954C	0.1 mm H <sub>2</sub> O/cm <sup>2</sup>
	Latex Particle Challenge (Filtration Efficiency) @ 0.1 micron per ASTM F2299	41.6%
	Bacterial Filtration Efficiency	16.0%
	Helmke Drum - Ear Loops	Category 1
	Helmke Drum - Ties	Category 2

## Comfort™ Veil

### Designed Especially for Users with Sensitive Skin

**Features & Benefits:** To help wearers with sensitive skin, the Comfort™ Veil is made from a soft, nonwoven, hypo-allergenic material. The veil is (15") long to provide freedom of movement and better protection while employing a latex-free, elastic Comfort headband. An integrated malleable nosestrip is ultrasonically welded into the fabric to provide a good seal every time.



9400

### Comfort™ Veil

9400 Comfort™ Band  
150/case

Performance	Test Performed	Result (Average)
	Differential Pressure per MIL-M36954C	0.1 mm H <sub>2</sub> O/cm <sup>2</sup>
Latex Particle Challenge (Filtration Efficiency) @ 0.1 micron per ASTM F2299	54%	

## Coverall® Face Shields

### Splash Protection

**Features and Benefits:** When you need total facial splash protection, choose the Coverall® face shield. The face shield's wrap-around design provides the wearer with great peripheral vision while acting as a protective shield against non-hazardous liquid splash and light particles in a Lab or Controlled Environment. The Coverall face shield is not ANSI Z87 rated for eye protection. You can wear the lightweight shield comfortably for long periods and it fits easily over prescription glasses or protective eyewear. A double-sided anti-fog coating reduces

the possibility of fogging in high humidity environments. For safe working conditions, the face shield is low distorting and 100% optically clear while a soft polyurethane foam headband securely positions the device on the wearer.

Available in two styles: Full face shield and half face shield. Also available with an adjustable Velcro® band or with our latex free elastic Comfort headband. Individually packaged.



2807

### Coverall® Full Face Shields

2802 Full Face Shield w/Velcro® Adjustable Band  
2807 Full Face Shield w/Comfort Band  
100/case (4 boxes of 25)



2808


### Coverall® Half Face Shields

2803 Half Face Shield w/Velcro® Adjustable Band  
2808 Half Face Shield w/Comfort Band  
100/case (4 boxes of 25)



## Facemask Packaging


### *Dispenser Box Packaging*



**Dispenser Boxes**



**Dispenser boxes in carton**



**Carton taped sealed**


### *Cleanroom Packaging*



**Masks in heat-sealed bag**



**Mask bags in carton  
liner within carton**



**Carton taped sealed**